

C3R30248SC Cut Sheet



Hammond enclosure, NEMA 3R, 30 x 24 x 8in (HxWxD), wall mount, with knockouts, galvanized steel, ANSI 61 gray, powder coat finish, screw cover with handles, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R30248SC>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
NEMA Rating	3R
IP Rating	IP24
Nominal Enclosure Dimensions	30 x 24 x 8in (HxWxD)
Enclosure Height	30.17in
Enclosure Width	24.52in
Enclosure Depth	8.32in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	Yes
Material	Galvanized steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover with handles
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL21312
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document