

# C3R303016HCR Cut Sheet



Hammond enclosure, NEMA 3R, 30 x 30 x 16in (HxWxD), wall mount, galvanized steel, ANSI 61 gray, powder coat finish, hinged screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R303016HCR>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Hammond                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R                           |
| <b>IP Rating</b>                    | IP24                         |
| <b>Nominal Enclosure Dimensions</b> | 30 x 30 x 16in (HxWxD)       |
| <b>Enclosure Height</b>             | 30.33in                      |
| <b>Enclosure Width</b>              | 30.31in                      |
| <b>Enclosure Depth</b>              | 16.34in                      |
| <b>Mounting</b>                     | Wall                         |
| <b>Integral Mounting Feet</b>       | No                           |

|                                  |                         |
|----------------------------------|-------------------------|
| <b>Integral Mounting Flange</b>  | Yes                     |
| <b>Dual Access</b>               | No                      |
| <b>Knockouts</b>                 | No                      |
| <b>Bottom Gland Plate</b>        | No                      |
| <b>Material</b>                  | Galvanized steel        |
| <b>Color</b>                     | ANSI 61 gray            |
| <b>Finish</b>                    | Powder coat             |
| <b>Cover Type</b>                | Hinged screw cover      |
| <b>Hinge Type</b>                | Continuous hinge        |
| <b>Number of Hinges Per Door</b> | 1                       |
| <b>Padlock Attachment Type</b>   | Padlock hasp and staple |
| <b>Shelf</b>                     | No                      |
| <b>Padlockable</b>               | Yes                     |
| <b>Keylocking</b>                | No                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LL21312                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/C3R303016HCR.pdf>  
See store item page for other formats.