

C3R363612HCR Cut Sheet



Hammond enclosure, NEMA 3R, 36 x 36 x 12in (HxWxD), wall mount, galvanized steel, ANSI 61 gray, powder coat finish, hinged screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R363612HCR>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R
IP Rating	IP24
Nominal Enclosure Dimensions	36 x 36 x 12in (HxWxD)
Enclosure Height	36.33in
Enclosure Width	36.31in
Enclosure Depth	12.34in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Galvanized steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Hinged screw cover
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Padlock Attachment Type	Padlock hasp and staple
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL21312
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C3R363612HCR.pdf>
See store item page for other formats.