

C3R664SCNKO Cut Sheet



Hammond enclosure, NEMA 3R, 6 x 6 x 4in (HxWxD), wall mount, galvanized steel, ANSI 61 gray, powder coat finish, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3R664SCNKO>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
NEMA Rating	3R
IP Rating	IP24
Nominal Enclosure Dimensions	6 x 6 x 4in (HxWxD)
Enclosure Height	6.12in
Enclosure Width	6.49in
Enclosure Depth	4.28in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Galvanized steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LL21312
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document