

C3RWT418 Cut Sheet



Hammond wiring trough, 4 x 4 x 18in (HxDxL), NEMA 3R, wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3RWT418>

Technical Specifications

Brand	Hammond
Item	Wiring trough
NEMA Rating	3R
IP Rating	IP24
Nominal Enclosure Dimensions	4 x 18 x 4in (HxWxD)
Enclosure Height	4.00in
Enclosure Depth	4.44in
Enclosure Length	18.88in

Mounting	Wall
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Padlockable	Yes
Padlock Attachment Type	Padlock hasp and staple

Agency Approvals

UL Listed File #	E186830
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C3RWT418.pdf>
See store item page for other formats.