

# C3SC18186GY Cut Sheet



Hammond enclosure, NEMA 3/4/12, 18 x 18 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3SC18186GY>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Hammond               |
| <b>Item</b>                         | Enclosure             |
| <b>Slope Top</b>                    | No                    |
| <b>3-Piece Assembly</b>             | No                    |
| <b>Vented</b>                       | No                    |
| <b>NEMA Rating</b>                  | 3/4/12                |
| <b>IP Rating</b>                    | IP66                  |
| <b>Nominal Enclosure Dimensions</b> | 18 x 18 x 6in (HxWxD) |
| <b>Enclosure Height</b>             | 18.19in               |
| <b>Enclosure Width</b>              | 18.19in               |
| <b>Enclosure Depth</b>              | 6.23in                |
| <b>Mounting</b>                     | Wall                  |

|                                 |              |
|---------------------------------|--------------|
| <b>Integral Mounting Feet</b>   | No           |
| <b>Integral Mounting Flange</b> | No           |
| <b>Dual Access</b>              | No           |
| <b>Knockouts</b>                | No           |
| <b>Bottom Gland Plate</b>       | No           |
| <b>Material</b>                 | Carbon steel |
| <b>Color</b>                    | ANSI 61 gray |
| <b>Finish</b>                   | Powder coat  |
| <b>Cover Type</b>               | Screw cover  |
| <b>Shelf</b>                    | No           |
| <b>Padlockable</b>              | No           |
| <b>Keylocking</b>               | No           |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/C3SC18186GY.pdf>  
See store item page for other formats.