

# C3SC884GY Cut Sheet



Hammond enclosure, NEMA 3/4/12, 8 x 8 x 4in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C3SC884GY>

## Technical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Brand</b>                        | Hammond             |
| <b>Item</b>                         | Enclosure           |
| <b>Slope Top</b>                    | No                  |
| <b>3-Piece Assembly</b>             | No                  |
| <b>Vented</b>                       | No                  |
| <b>NEMA Rating</b>                  | 3/4/12              |
| <b>IP Rating</b>                    | IP66                |
| <b>Nominal Enclosure Dimensions</b> | 8 x 8 x 4in (HxWxD) |
| <b>Enclosure Height</b>             | 8.19in              |
| <b>Enclosure Width</b>              | 8.19in              |
| <b>Enclosure Depth</b>              | 4.17in              |
| <b>Mounting</b>                     | Wall                |
| <b>Integral Mounting Feet</b>       | No                  |
| <b>Integral Mounting Flange</b>     | No                  |
| <b>Dual Access</b>                  | No                  |
| <b>Knockouts</b>                    | No                  |
| <b>Bottom Gland Plate</b>           | No                  |
| <b>Material</b>                     | Carbon steel        |
| <b>Color</b>                        | ANSI 61 gray        |
| <b>Finish</b>                       | Powder coat         |
| <b>Cover Type</b>                   | Screw cover         |
| <b>Padlockable</b>                  | No                  |
| <b>Keylocking</b>                   | No                  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |