

# CC600-14-2U-1 Cut Sheet



Quabbin control cable, unshielded, 2 conductors, 14 AWG, 41-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-14-2U-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 2586
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V rated (UL)
<b>Conductors</b>	2 conductors
<b>Conductor Size</b>	14 AWG
<b>Conductor Stranding</b>	41-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC

<b>Conductor Insulation Color</b>	Black and brown
<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.271in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 50ft = Coil, 51 to 530ft = 14 x 7in Reel, 531 to 760ft = 14 x 10in Reel, 761 to 1165ft = 16 x 10in Reel, 1166 to 1625ft = 18 x 10in Reel, 1626 to 2115ft = 18 x 13in Reel, 2116 to 4730ft = 24 x 17in Wooden Reel, 4731 to 5000ft = 30 x 17in Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E69976
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>