


# CC600-16-12U-1 Cut Sheet



Quabbin flexible control cable, unshielded, 12 conductors, 16 AWG, 19-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-16-12U-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 2586
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V rated (UL)
<b>Conductors</b>	12 conductors
<b>Conductor Size</b>	16 AWG
<b>Conductor Stranding</b>	19-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black, brown, red, orange, yellow, green, blue, violet, gray, white, white/black and white/brown

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.427in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 20 to 50ft = Coil</li><li>• 51 to 215ft = 14 x 7in Reel</li><li>• 216 to 305ft = 14 x 10in Reel</li><li>• 306 to 470ft = 16 x 10in Reel</li><li>• 471 to 655ft = 18 x 10in Reel</li><li>• 656 to 850ft = 18 x 13in Reel</li><li>• 851 to 1905ft = 24 x 17in Wooden Reel</li><li>• 1906 to 3045ft = 30 x 17in Wooden Reel</li><li>• 3046 to 5000ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E69976
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>