

CC600-16-4S-1 Cut Sheet



Quabbin control cable, shielded, 4 conductors, 16 AWG, 19-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-16-4S-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control
UL Wire/Cable Type	AWM
Applicable Standards	UL 2586
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V rated (UL)
Conductors	4 conductors
Conductor Size	16 AWG
Conductor Stranding	19-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, brown, red and orange

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.304in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 448ft = 14 x 7in Reel, 449 to 489ft = 14 x 10in Reel, 490 to 699ft = 16 x 10in Reel, 700 to 1082ft = 18 x 10in Reel, 1083 to 1524ft = 18 x 13in Reel, 1525 to 1981ft = 24 x 17in Wooden Reel, 1982 to 4254ft = 30 x 17in Wooden Reel, 4255 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement