


CC600-18-12S-1 Cut Sheet



Quabbin flexible control cable, shielded, 12 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-18-12S-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control
UL Wire/Cable Type	AWM
Applicable Standards	UL 2586
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V rated (UL)
Conductors	12 conductors
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, brown, red, orange, yellow, green, blue, violet, gray, white, white/black and white/brown

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.382in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 265ft = 14 x 7in Reel, 266 to 380ft = 14 x 10in Reel, 381 to 585ft = 16 x 10in Reel, 586 to 820ft = 18 x 10in Reel, 821 to 1065ft = 18 x 13in Reel, 1066 to 2380ft = 24 x 17in Wooden Reel, 2381 to 3805ft = 30 x 17in Wooden Reel, 3806 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement