


# CC600-18-19U-1 Cut Sheet



Quabbin control cable, unshielded, 19 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-18-19U-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 2586
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V rated (UL)
<b>Conductors</b>	19 conductors
<b>Conductor Size</b>	18 AWG
<b>Conductor Stranding</b>	16-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black, brown, red, orange, yellow, green, blue, violet, gray, white, white/black, white/brown, white/red, white/orange, white/yellow, white/green, white/blue, white/violet and white/gray

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.452in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 50ft = Coil, 51 to 190ft = 14 x 7in Reel, 191 to 275ft = 14 x 10in Reel, 276 to 420ft = 16 x 10in Reel, 421 to 585ft = 18 x 10in Reel, 586 to 760ft = 18 x 13in Reel, 761 to 1700ft = 24 x 17in Wooden Reel, 1701 to 2720ft = 30 x 17in Wooden Reel, 2721 to 5000ft = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E69976
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL51726
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>