

CC600-20-3U-1 Cut Sheet



Quabbin control cable, unshielded, 3 conductors, 20 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CC600-20-3U-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control
UL Wire/Cable Type	AWM
Applicable Standards	UL 2586
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V rated (UL)
Conductors	3 conductors
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black, brown and red
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.218in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 820ft = 14 x 7in Reel, 821 to 1170ft = 14 x 10in Reel, 1171 to 1795ft = 16 x 10in Reel, 1796 to 2510ft = 18 x 10in Reel, 2511 to 3265ft = 18 x 13in Reel, 3266 to 7305ft = 24 x 17in Wooden Reel, 7306 to 10000ft = 30 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E69976
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement