


CD08-0A-070-A1 Cut Sheet

AutomationDirect connection cable, M8 axial female to pigtail, 3-pole, PVC jacket, gray, 22.9ft/7m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CD08-0A-070-A1>



Technical Specifications

Brand	AutomationDirect
Item	Cable
Cable Type	Connection
Connection 1	M8 axial female
Connection 2	Pigtail
Number of Poles	3
Jacket Material	PVC
Jacket Color	Gray
Cable Length	22.9ft/7m
IP Rating	IP67

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	080128_0_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CD08-0A-070-A1.pdf>
See store item page for other formats.