

# CD08-0A-070-C1 Cut Sheet



AutomationDirect connection cable, M8 right-angle female to pigtail, 3-pole, PVC jacket, gray, 22.9ft/7m cable length, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CD08-0A-070-C1>

## Technical Specifications

|                        |                       |
|------------------------|-----------------------|
| <b>Brand</b>           | AutomationDirect      |
| <b>Item</b>            | Cable                 |
| <b>Cable Type</b>      | Connection            |
| <b>Connection 1</b>    | M8 right-angle female |
| <b>Connection 2</b>    | Pigtail               |
| <b>Number of Poles</b> | 3                     |
| <b>Jacket Material</b> | PVC                   |
| <b>Jacket Color</b>    | Gray                  |
| <b>Cable Length</b>    | 22.9ft/7m             |
| <b>IP Rating</b>       | IP67                  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 080128_0_000                           |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |