

CDC-18X20RV39N Cut Sheet



Murrplastik MP45 pretensioned cable drag chain, 1.77in inside height, 1.97in inside width, 3.94in bend radius, inside opening, 2.64in pitch, 3.2ft/1m length, black. Requires CDC-KAZ-18X20 bracket for mounting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CDC-18X20RV39N>

Technical Specifications

Brand	Murrplastik
Series	MP45
Item	Cable drag chain
Pretensioned	Yes
Inside Height	1.77in
Inside Width	1.97in
Bend Radius	3.94in
Opening	Inside
Pitch	2.64in
Length	3.2ft/1m
Color	Black
Requires	CDC-KAZ-18X20 bracket for mounting

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CDC-18X20RV39N.pdf>
See store item page for other formats.