

CDP12-0B-010-AA Cut Sheet



AutomationDirect connection cable, M12 axial female to axial male, 4-pole, PVC jacket, gray, 3.2ft/1m cable length, IP67, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CDP12-0B-010-AA>

Technical Specifications

Brand	AutomationDirect
Item	Cable
Cable Type	Connection
Connection 1	M12 axial female
Connection 2	Axial male
Number of Poles	4
Jacket Material	PVC
Jacket Color	Gray
Cable Length	3.2ft/1m
IP Rating	IP67
Application	Sensor & signal

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	080128_0_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CDP12-0B-010-AA.pdf>
See store item page for other formats.