

CDP12-0B-010-BB Cut Sheet

AutomationDirect connection cable, M12 right-angle female to right-angle male, 4-pole, PVC jacket, gray, 3.2ft/1m cable length, IP67, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CDP12-0B-010-BB>



Technical Specifications

| | |
|-----------------|------------------------|
| Brand | AutomationDirect |
| Item | Cable |
| Cable Type | Connection |
| Connection 1 | M12 right-angle female |
| Connection 2 | Right-angle male |
| Number of Poles | 4 |
| Jacket Material | PVC |
| Jacket Color | Gray |
| Cable Length | 3.2ft/1m |
| IP Rating | IP67 |
| Application | Sensor & signal |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 080128_0_000 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CDP12-0B-010-BB.pdf>
See store item page for other formats.