

CF-DB1-20 Cut Sheet



AutomationDirect optical fiber, plastic, cuttable, diffuse, M6 head, nickel-plated brass, polyethylene jacket, 200mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF-DB1-20>

Technical Specifications

Brand	AutomationDirect
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Diffuse
Head Size	M6
Head Material	Nickel-plated brass
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	200mm
Length	2m
Includes	Fiber cutter and mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
RoHS Status	No
EU REACH	View EU REACH document