

CF-TB4-20 Cut Sheet



AutomationDirect optical fiber, plastic, cuttable, through-beam, M6 head, nickel-plated brass, 90-degree, polyethylene jacket, 1800mm sensing distance, 2m length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF-TB4-20>

Technical Specifications

Brand	AutomationDirect
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Through-beam
Head Size	M6
Head Material	Nickel-plated brass
Head Angle	90-degree
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	1800mm
Length	2m
Quantity per Pack	2
Includes	Fiber cutter and mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
RoHS Status	No
EU REACH	View EU REACH document