


# CF10-UL-07-04-1 Cut Sheet



igus continuous flexing control cable, shielded, 4 conductors (includes ground), 18 AWG (0.75mm<sup>2</sup>), bare copper, TPE conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF10-UL-07-04-1>

## Technical Specifications

<b>Brand</b>	igus
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Control
<b>UL Wire/Cable Type</b>	AWM
<b>Applicable Standards</b>	UL 10258, UL 21387 and NFPA 79
<b>Application</b>	Automation
<b>Flexibility</b>	Continuous flexing
<b>Voltage Rating</b>	600V (AWM Style 10258), 1000V (AWM Style 21387)
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	18 AWG (0.75mm <sup>2</sup> )
<b>Conductor Stranding</b>	42-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	TPE
<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground

<b>Shielding</b>	Shielded
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Gray
<b>Nominal Overall Cable Diameter</b>	0.354in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 75ft = Coil, 76 to 310ft = 14 x 7in Reel, 311 to 440ft = 14 x 10in Reel, 441 to 690ft = 16 x 10in Reel, 691 to 970ft = 18 x 10in Reel, 971 to 1260ft = 18 x 13in Reel, 1261 to 2710ft = 24 x 17in Wooden Reel, 2711 to 4460ft = 30 x 17in Wooden Reel, 4461 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E310776
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>