

CF11-02-03-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, 3 twisted pairs, 24 AWG (0.25mm²), bare copper, TPE conductor insulation material, pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink, TPE jacket, blue, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF11-02-03-02-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	3 twisted pairs
Conductor Size	24 AWG (0.25mm ²)
Conductor Stranding	32-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE
Conductor Insulation Color	Pair 1: white and brown, pair 2: green and yellow and pair 3: grey and pink

Shielding	Shielded
Jacket Material	TPE
Jacket Color	Blue
Nominal Overall Cable Diameter	0.315in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 395ft = 14 x 7in Reel• 396 to 560ft = 14 x 10in Reel• 561 to 860ft = 16 x 10in Reel• 861 to 1205ft = 18 x 10in Reel• 1206 to 1500ft = 18 x 13in Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document