


CF130US-15-18-1 Cut Sheet



igus continuous flexing control cable, unshielded, 18 conductors (includes ground), 16 AWG (1.50mm²), bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF130US-15-18-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control
UL Wire/Cable Type	TC, TC-ER, WTTTC and MTW
Applicable Standards	UL 2587
Application	Automation
Flexibility	Continuous flexing
Voltage Rating	600V
Conductors	18 conductors (includes ground)
Conductor Size	16 AWG (1.50mm ²)
Conductor Stranding	30-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.65in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 90ft = 14 x 7in Reel, 91 to 120ft = 14 x 10in Reel, 121 to 200ft = 16 x 10in Reel, 201 to 280ft = 18 x 10in Reel, 281 to 360ft = 18 x 13in Reel, 361 to 780ft = 24 x 17in Wooden Reel, 781 to 1290ft = 30 x 17in Wooden Reel, 1291 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E223775
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	257958
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document