

CF130US-25-07-1 Cut Sheet



igus continuous flexing control cable, unshielded, 7 conductors (includes ground), 14 AWG (2.50mm²), bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF130US-25-07-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control
UL Wire/Cable Type	TC, TC-ER, WTTC and MTW
Applicable Standards	UL 2587
Application	Automation
Flexibility	Continuous flexing
Voltage Rating	600V
Conductors	7 conductors (includes ground)
Conductor Size	14 AWG (2.50 mm ²)
Conductor Stranding	50-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.51in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 150ft = 14 x 7in Reel, 151 to 210ft = 14 x 10in Reel, 211 to 330ft = 16 x 10in Reel, 331 to 460ft = 18 x 10in Reel, 461 to 600ft = 18 x 13in Reel, 601 to 1310ft = 24 x 17in Wooden Reel, 1311 to 2150ft = 30 x 17in Wooden Reel, 2151 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E223775
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	257958
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document