

CF1432 Cut Sheet



Stahlin CF series pushbutton enclosure, blank cover, NEMA 1/3R/4X/6P/12, 14 x 3 x 2in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF1432>

Technical Specifications

| | |
|-------------------------------------|---------------------------------|
| Brand | Stahlin |
| Item | Pushbutton enclosure |
| Series | CF |
| Number of Pushbutton Holes | Blank cover |
| Slope Top | No |
| NEMA Rating | 1/3R/4X/6P/12 |
| IP Rating | IP68 |
| Nominal Enclosure Dimensions | 14 x 3 x 2in (HxWxD) |
| Enclosure Height | 13.78in |
| Enclosure Width | 3.63in |
| Enclosure Depth | 3.14in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Crowned screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64358 |
| UL Recognized File # | E333478 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR069014 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |