


CF211-02-02-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, AWM, 2 twisted pairs, 24 AWG (0.25mm²), bare copper, TPE conductor insulation material, pair 1: white and brown and pair 2: green and yellow, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF211-02-02-02-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	2 twisted pairs
Conductor Size	24 AWG (0.25mm ²)
Conductor Stranding	32-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE

Conductor Insulation Color	Pair 1: white and brown and pair 2: green and yellow
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.256in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 590ft = 14 x 7in Reel, 591 to 850ft = 14 x 10in Reel, 851 to 1320ft = 16 x 10in Reel, 1321 to 1615ft = 18 x 10in Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E310776
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document