


CF211-05-04-02-1 Cut Sheet



igus continuous flexing control and signal cable, shielded, 4 twisted pairs, 20 AWG (0.50mm²), 28-stranded, bare copper, TPE conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF211-05-04-02-1>

Technical Specifications

Brand	igus
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Continuous flexing
Voltage Rating	300V
Conductors	4 twisted pairs
Conductor Size	20 AWG (0.50mm ²)
Conductor Stranding	28-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE

Conductor Insulation Color	Pair 1: white and brown, pair 2: green and yellow, pair 3: grey and pink and pair 4: blue and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.374in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 280ft = 14 x 7in Reel• 281 to 400ft = 14 x 10in Reel• 401 to 610ft = 16 x 10in Reel• 611 to 855ft = 18 x 10in Reel• 856 to 1110ft = 18 x 13in Reel• 1111 to 1500ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E310776
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document