


CF30-15-04-1 Cut Sheet

igus continuous flexing motor supply cable, unshielded, 4 conductors (includes ground), 16 AWG (1.50mm²), bare copper, TPE conductor insulation material, black with white print and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF30-15-04-1>



Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | igus |
| Item | Cable |
| Wire/Cable Type | Motor supply |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 10492, UL 2570 and NFPA 79 |
| Application | Drive and motor |
| Flexibility | Continuous flexing |
| Voltage Rating | 1000V |
| Conductors | 4 conductors (includes ground) |
| Conductor Size | 16 AWG (1.50mm ²) |
| Conductor Stranding | 30-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | TPE |

| | |
|---------------------------------------|---|
| Conductor Insulation Color | Black with white print and green/yellow ground |
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.334in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 350ft = 14 x 7in Reel• 351 to 500ft = 14 x 10in Reel• 501 to 765ft = 16 x 10in Reel• 766 to 1070ft = 18 x 10in Reel• 1071 to 1390ft = 18 x 13in Reel• 1391 to 1500ft = 24 x 17in Wooden Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E310776 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |