


CF30-350-04-1 Cut Sheet

igus continuous flexing motor supply cable, unshielded, 4 conductors (includes ground), 2 AWG (35mm²), bare copper, TPE conductor insulation material, black with white print and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF30-350-04-1>

Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | igus |
| Item | Cable |
| Wire/Cable Type | Motor supply |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 10492, UL 2570 and NFPA 79 |
| Application | Drive and motor |
| Flexibility | Continuous flexing |
| Voltage Rating | 1000V |
| Conductors | 4 conductors (includes ground) |
| Conductor Size | 2 AWG (35mm ²) |
| Conductor Stranding | 280-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | TPE |

| | |
|---------------------------------------|---|
| Conductor Insulation Color | Black with white print and green/yellow ground |
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 1.141in |
| Bulk Length | Cut to length |
| Package Type | 1 to 20ft = Coil, 21 to 30ft = 14 x 10in Reel, 31 to 50ft = 16 x 10in Reel, 51 to 80ft = 18 x 10in Reel, 81 to 100ft = 18 x 13in Reel, 101 to 220ft = 24 x 17in Wooden Reel, 221 to 370ft = 30 x 17in Wooden Reel, 371 to MAX = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E310776 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |