


CF30-60-04-1 Cut Sheet

igus continuous flexing motor supply cable, unshielded, 4 conductors (includes ground), 10 AWG (6mm²), bare copper, TPE conductor insulation material, black with white print and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF30-60-04-1>



Technical Specifications

| | |
|--------------------------------------|--|
| Brand | igus |
| Item | Cable |
| Wire/Cable Type | Motor supply |
| UL Wire/Cable Type | AWM |
| Applicable Standards | UL 10492, UL 2570 and NFPA 79 |
| Application | Drive and motor |
| Flexibility | Continuous flexing |
| Voltage Rating | 1000V |
| Conductors | 4 conductors (includes ground) |
| Conductor Size | 10 AWG (6mm ²) |
| Conductor Stranding | 84-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | TPE |
| Conductor Insulation Color | Black with white print and green/yellow ground |

| | |
|---------------------------------------|---|
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.551in |
| Bulk Length | Cut to length |
| Package Type | 1 to 50ft = Coil, 51 to 120ft = 14 x 7in Reel, 121 to 180ft = 14 x 10in Reel, 181 to 280ft = 16 x 10in Reel, 281 to 400ft = 18 x 10in Reel, 401 to 520ft = 18 x 13in Reel, 521 to 1120ft = 24 x 17in Wooden Reel, 1121 to 1840ft = 30 x 17in Wooden Reel, 1841 to MAX = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E310776 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |