

CF4PB22 Cut Sheet



Stahlin CF series pushbutton enclosure, 4 holes, 22mm, NEMA 1/3R/4X/6P/12, 8 x 4 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF4PB22>

Technical Specifications

Brand	Stahlin
Item	Pushbutton enclosure
Series	CF
Number of Pushbutton Holes	4 holes
Pushbutton Hole Nominal Size	22mm
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP68
Nominal Enclosure Dimensions	8 x 4 x 4in (HxWxD)
Enclosure Height	8.88in

Enclosure Width	3.81in
Enclosure Depth	3.89in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CF4PB22.pdf>
See store item page for other formats.