

CFS-1PCC30-DC Cut Sheet



Gladiator CFS series disconnect switch, fusible, Class CC, load break capable, 1-pole, 80 VDC, 30A, 200kA SCCR, DIN rail mount, UL 98 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CFS-1PCC30-DC>

Technical Specifications

Brand	Gladiator
Item	Disconnect switch
Series	CFS
Fuse Class	Class CC
Fusible	Yes
Load Break Capable	Yes
Number of Poles	1

Voltage Rating	80 VDC
Amperage Rating	30A
SCCR Rating	200kA SCCR
Mounting	DIN rail
UL Rating	UL 98 rated
Additional Information	6-18 AWG single or dual wire rated, 4AWG single wire rated, solid or stranded wire

Agency Approvals

UL Listed File #	E339079
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CFS-1PCC30-DC.pdf>
See store item page for other formats.