

# CFS-1PCC30-DC Cut Sheet



Gladiator CFS series disconnect switch, fusible, Class CC, load break capable, 1-pole, 80 VDC, 30A, 200kA SCCR, DIN rail mount, UL 98 rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CFS-1PCC30-DC>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Disconnect switch
<b>Series</b>	CFS
<b>Fuse Class</b>	Class CC
<b>Fusible</b>	Yes
<b>Load Break Capable</b>	Yes
<b>Number of Poles</b>	1
<b>Voltage Rating</b>	80 VDC
<b>Amperage Rating</b>	30A
<b>SCCR Rating</b>	200kA SCCR
<b>Mounting</b>	DIN rail
<b>UL Rating</b>	UL 98 rated
<b>Additional Information</b>	6-18 AWG single or dual wire rated, 4AWG single wire rated, solid or stranded wire

## Agency Approvals

<b>UL Listed File #</b>	E339079
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None