

CFW100-IOADR Cut Sheet



WEG Electric CFW100 series temperature combo module with infrared remote control, thermistor, 1-channel input, 3-point output, 240 VAC, (3) Form A (SPST) relays. For use with WEG CFW100 series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CFW100-IOADR>

Technical Specifications

Brand	WEG Electric
Item	Combo module with infrared remote control
I/O Module Type	Temperature
Input Signal Type(s)	Thermistor
Series	CFW100
Number Of Input Channels	1
Input Thermistor Signal Types	10K B3435 K
Number of Output Points	3
Nominal Output Voltage	240 VAC
Discrete Output Type	Relay
Relay Configuration	(3) Form A (SPST) relays

Load Current	0.5A/point
Number of Isolated Discrete Output Commons	3
Number of Points per Discrete Output Common	1
For Use With	WEG CFW100 series AC drives
Includes	(1) NTC sensor, (1) 3.2ft/1m sensor cable, (1) infrared remote control with battery and (1) 4.9ft/1.5m infrared receiver cable
Additional Information	Infrared receiver cable for remote control signal connects to unit via (1) 3.5mm mini jack

Agency Approvals

UL Listed File #	E184430
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CFW100-IOADR.pdf>
See store item page for other formats.