

CH30J3 Cut Sheet



Bussmann modular fuse holder, accepts Class J fuses, 30A, 600 VAC/VDC or less, 3-pole, 18-1 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail or panel mount. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CH30J3>

Technical Specifications

Brand	Bussmann
Item	Fuse holder
Modular	Yes
Blown Fuse Indicator	No
Multi-Wire	No
Accepts Fuse Class	Class J
Amperage Rating	30A
Voltage Rating	600 VAC/VDC or less

Number of Poles	3
Conductor Size	18-1 AWG copper only
Conductor Connection Type	Integral pressure plate with separate spade connection
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail or panel
Quantity per Pack	2

Agency Approvals

UL Listed File #	E14853
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	047235
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CH30J3.pdf>
See store item page for other formats.