

CHKO16126 Cut Sheet



Hammond enclosure, NEMA 1, 16 x 12 x 6in (HxWxD), wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHKO16126>

Technical Specifications

Brand	Hammond	Dual Access	No
Item	Enclosure	Knockouts	Yes
Slope Top	No	Material	Carbon steel
NEMA Rating	1	Color	ANSI 61 gray
IP Rating	IP30	Finish	Powder coat
Nominal Enclosure Dimensions	16 x 12 x 6in (HxWxD)	Cover Type	Single-door
Enclosure Height	16.38in	Hinge Type	Butt hinges
Enclosure Width	12.30in	Number of Hinges Per Door	2
Enclosure Depth	6.12in	Latch Type	1/4-turn flush-mounted latch
Mounting	Wall	Number Of Latches	1
Integral Mounting Feet	No	Padlockable	No
Integral Mounting Flange	No	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR21001
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document