

CHKO36248 Cut Sheet



Hammond enclosure, NEMA 1, 36 x 24 x 8in (HxWxD), wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHKO36248>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1
IP Rating	IP30
Nominal Enclosure Dimensions	36 x 24 x 8in (HxWxD)
Enclosure Height	36.38in
Enclosure Width	24.30in
Enclosure Depth	8.13in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	Yes
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Butt hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn flush-mounted latch
Number Of Latches	1
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR21001
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CHKO36248.pdf>
See store item page for other formats.