

CHSC-AL-1 Cut Sheet



ProSense general purpose screw cover connection head, 1/2in female NPT probe connection, 3/4in female NPT conduit opening, maximum temperature rating of 825 deg F (440 deg C), die-cast aluminum, NEMA 4X, IP66.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHSC-AL-1>

Technical Specifications

Brand	ProSense
Item	General purpose screw cover connection head
Probe Connection	1/2in female NPT
Electrical Connection	3/4in female NPT conduit opening
Operating Temperature	Maximum temperature rating of 825 deg F (440 deg C)
Material	Die-cast aluminum
NEMA Rating	4X
IP Rating	IP66
For Use With	ProSense temperature probes
Includes	Graphite gasket
Additional Information	Order probe and terminal base separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document