

# CHT12-159B-30 Cut Sheet



Captron capacitive pushbutton sensor switch, IP69K, 22mm, toggle, aluminum bezel, manual LED control, Operator: white, 28.5mm. Requires 5-pin female M8 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHT12-159B-30>

## Technical Specifications

|                           |                                     |
|---------------------------|-------------------------------------|
| <b>Brand</b>              | Captron                             |
| <b>Item</b>               | Capacitive pushbutton sensor switch |
| <b>IP Rating</b>          | IP69K                               |
| <b>Barrel Size</b>        | 22mm                                |
| <b>Action</b>             | Toggle                              |
| <b>Bulb Type</b>          | LED illuminated                     |
| <b>Output</b>             | PNP, N.O.                           |
| <b>Contact Type</b>       | (1) N.O.                            |
| <b>Light Color(s)</b>     | Red/green                           |
| <b>LED Control</b>        | Manual                              |
| <b>Base Material</b>      | Plastic                             |
| <b>Bezel Material</b>     | Aluminum                            |
| <b>Bezel Color</b>        | Silver                              |
| <b>Operator Color</b>     | White                               |
| <b>Operator Type</b>      | Flush                               |
| <b>Operator Size</b>      | 28.5mm                              |
| <b>Operator Shape</b>     | Round                               |
| <b>Operator Material</b>  | Polycarbonate                       |
| <b>Voltage Rating</b>     | 10-30 VDC                           |
| <b>Voltage Regulation</b> | Full voltage                        |
| <b>Requires</b>           | 5-pin female M8 cable               |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 270141                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |