

CHT12-159P-30 Cut Sheet



Captron capacitive pushbutton sensor switch, IP69K, 22mm, toggle, aluminum bezel, semi-automatic LED control, Operator: white, 28.5mm. Requires 4-pin female M8 cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHT12-159P-30>

Technical Specifications

| | |
|---------------------------|-------------------------------------|
| Brand | Captron |
| Item | Capacitive pushbutton sensor switch |
| IP Rating | IP69K |
| Barrel Size | 22mm |
| Action | Toggle |
| Bulb Type | LED illuminated |
| Output | PNP, N.O. |
| Contact Type | (1) N.O. |
| Light Color(s) | Red/green |
| LED Control | Semi-automatic |
| Base Material | Plastic |
| Bezel Material | Aluminum |
| Bezel Color | Silver |
| Operator Color | White |
| Operator Type | Flush |
| Operator Size | 28.5mm |
| Operator Shape | Round |
| Operator Material | Polycarbonate |
| Voltage Rating | 10-30 VDC |
| Voltage Regulation | Full voltage |
| Requires | 4-pin female M8 cable |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 270141 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |