

# CHT3-15XB-30-TGSR Cut Sheet



Captron capacitive pushbutton sensor switch, IP69K, 50mm, dynamic, polycarbonate bezel, manual LED control, Operator: white, 88mm. Requires 5-pin female M8 cable and AR3 cover ring.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHT3-15XB-30-TGSR>

## Technical Specifications

<b>Brand</b>	Captron
<b>Item</b>	Capacitive pushbutton sensor switch
<b>IP Rating</b>	IP69K
<b>Barrel Size</b>	50mm
<b>Action</b>	Dynamic
<b>Bulb Type</b>	LED illuminated
<b>Output</b>	PNP, N.O.
<b>Contact Type</b>	(1) N.O.
<b>Light Color(s)</b>	Red/green
<b>LED Control</b>	Manual
<b>Base Material</b>	Plastic
<b>Bezel Material</b>	Polycarbonate
<b>Operator Color</b>	White
<b>Operator Type</b>	Flush
<b>Operator Size</b>	88mm
<b>Operator Shape</b>	Round
<b>Operator Material</b>	Polycarbonate
<b>Voltage Rating</b>	24 VDC
<b>Voltage Regulation</b>	Full voltage
<b>Requires</b>	5-pin female M8 cable and AR3 cover ring

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	270141
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>