

CHT3-15XP-29-TGSR Cut Sheet



Captron capacitive pushbutton sensor switch, IP69K, 50mm, dynamic, polycarbonate bezel, semi-automatic LED control, Operator: white, 88mm, operator text "START", green. Requires 4-pin female M8 cable and AR3 cover ring.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CHT3-15XP-29-TGSR>

Technical Specifications

Brand	Captron
Item	Capacitive pushbutton sensor switch
IP Rating	IP69K
Barrel Size	50mm
Action	Dynamic
Bulb Type	LED illuminated
Output	PNP, N.O.
Contact Type	(1) N.O.
Light Color(s)	Red/green
LED Control	Semi-automatic
Base Material	Plastic

Bezel Material	Polycarbonate
Operator Color	White
Operator Type	Flush
Operator Size	88mm
Operator Shape	Round
Operator Material	Polycarbonate
Operator Legend	START
Text Color	Green
Voltage Rating	24 VDC
Voltage Regulation	Full voltage
Requires	4-pin female M8 cable and AR3 cover ring

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	270141
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CHT3-15XP-29-TGSR.pdf>
See store item page for other formats.