

CK1-00-2H Cut Sheet



AutomationDirect capacitive proximity sensor, tubular, 18mm diameter x 87mm body, polybutylene terephthalate housing, NPN/PNP, N.O./N.C. selectable output, 12mm sensing distance, non-flush, 10 Hz switching frequency, IP65 IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CK1-00-2H>

Technical Specifications

Brand	AutomationDirect	Operation Mode	N.O./N.C. selectable output
Item	Proximity sensor	Sensing Distance	12mm
Sensor Type	Capacitive	Mounting Type	Non-flush
Shape	Tubular	IO-Link Compatible	No
Housing Size	18mm diameter x 87mm body	Switching Frequency	10 Hz
Housing Material	Polybutylene terephthalate	Operating Voltage	10-36 VDC
Barrel Type	Threaded	IP Rating	IP65 IP67
Adjustable	Yes	Connection	4-pin M12 quick-disconnect
Number of Wires	3	Includes	Mounting hardware
Switching Output	NPN/PNP	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CK1-00-2H.pdf>
See store item page for other formats.