

CL1109W Cut Sheet



Stahlin Classic series enclosure, NEMA 1/3/3S/3R/4X/12, 11 x 9 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CL1109W>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	Classic
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3/3S/3R/4X/12
Nominal Enclosure Dimensions	11 x 9 x 6in (HxWxD)
Enclosure Height	11.21in
Enclosure Width	9.21in
Enclosure Depth	6.09in

Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Crowned screw cover
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CL1109W.pdf>
See store item page for other formats.