

CL1311HL Cut Sheet



Stahlin Classic series enclosure, NEMA 1/3/3S/3R/4X/12, 13 x 11 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned single-door, (1) 1/4-turn flush-mounted latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CL1311HL>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	Classic
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3/3S/3R/4X/12
Nominal Enclosure Dimensions	13 x 11 x 6in (HxWxD)
Enclosure Height	13.21in
Enclosure Width	11.21in
Enclosure Depth	6.59in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Crowned single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	1
Latch Type	(1) 1/4-turn flush-mounted latch
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CL1311HL.pdf>
See store item page for other formats.