

# CLC1-D-120 Cut Sheet



ProSense remote level controller, tank drain, (2) conductive level probes and (1) common probe input, (1) SPDT latching relay, fixed 1 second time delay output, 120 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLC1-D-120>

## Technical Specifications

Brand	ProSense
Item	Remote level controller
Application	Dual level probe automatic tank drain
Input	(2) conductive level probes and (1) common probe
Output	(1) SPDT latching relay, fixed 1 second time delay
Operating Voltage	120 VAC
Indicating Type	LED indicators for power, timing and relay status
Mounting	8-pin octal socket
Additional Information	Controller becomes UL listed when used with Macromatic 70169-D socket. Order socket and conductive level probes separately

## Agency Approvals

UL Listed File #	E191059
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CLC1-D-120.pdf>  
See store item page for other formats.