

# CLC1-F-240 Cut Sheet



ProSense remote level controller, tank fill, (2) conductive level probes and (1) common probe input, (1) SPDT latching relay, fixed 1 second time delay output, 240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLC1-F-240>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Remote level controller
<b>Application</b>	Dual level probe automatic tank fill
<b>Input</b>	(2) conductive level probes and (1) common probe
<b>Output</b>	(1) SPDT latching relay, fixed 1 second time delay
<b>Operating Voltage</b>	240 VAC
<b>Indicating Type</b>	LED indicators for power, timing and relay status
<b>Mounting</b>	8-pin octal socket
<b>Additional Information</b>	Controller becomes UL listed when used with Macromatic 70169-D socket. Order socket and conductive level probes separately

## Agency Approvals

<b>UL Listed File #</b>	E191059
<b>UL Recognized File #</b>	E191059
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	View EU REACH document

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CLC1-F-240.pdf>  
 See store item page for other formats.