

CLC1-F-240 Cut Sheet



ProSense remote level controller, tank fill, (2) conductive level probes and (1) common probe input, (1) SPDT latching relay, fixed 1 second time delay output, 240 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLC1-F-240>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | ProSense |
| Item | Remote level controller |
| Application | Tank fill |
| Input | (2) conductive level probes and (1) common probe |
| Output | (1) SPDT latching relay, fixed 1 second time delay |
| Operating Voltage | 240 VAC |
| Indicating Type | LED indicators for power, timing and relay status |
| Mounting | 8-pin octal socket |
| Additional Information | Controller becomes UL listed when used with Macromatic 70169-D socket. Order socket and conductive level probes separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191059 |
| UL Recognized File # | E191059 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CLC1-F-240.pdf>
See store item page for other formats.