

# CLT.10.2110R Cut Sheet



SapiSelco CLICK Tie series low temperature beaded releasable cable tie, 4.65in length, 0.13in width, 15.73lb tensile strength, 1.02in maximum bundle diameter, red, low-density polyethylene (LDPE). Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLT.10.2110R>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Low temperature beaded releasable
<b>Series</b>	CLICK Tie
<b>Length</b>	4.65in
<b>Width</b>	0.13in
<b>Tensile Strength</b>	15.73lb
<b>Maximum Bundle Diameter</b>	1.02in
<b>Color</b>	Red
<b>Material</b>	Low-density polyethylene (LDPE)
<b>Temperature Rating</b>	-58 to +140 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>