

# CLT.10.2157 Cut Sheet



SapiSelco CLICK Tie series low temperature beaded releasable cable tie, 25.31in length, 0.22in width, 61.82lb tensile strength, 7.08in maximum bundle diameter, red, low-density polyethylene (LDPE). Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLT.10.2157>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Low temperature beaded releasable
<b>Series</b>	CLICK Tie
<b>Length</b>	25.31in
<b>Width</b>	0.22in
<b>Tensile Strength</b>	61.82lb
<b>Maximum Bundle Diameter</b>	7.08in
<b>Color</b>	Red
<b>Material</b>	Low-density polyethylene (LDPE)
<b>Temperature Rating</b>	-58 to +140 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>